



Basic features

Исполнение	Соединительный кабель
Комплект поставки	Кабель
Применение	для видеодатчиков BVS HS-Q
Разрешение на эксплуатацию/конформность	cULus CE WEEE UKCA

Electrical connection

Диаметр кабеля D	5.50 mm
Кабель	TPE черный, 2 m
Разъем 1	RJ50-Штекер, прямой, 10-конт.
Разъем 2	D-SUB-Гнездо, прямой, 9-конт.
Сечение проводника	0.25 mm ²
Система	подготовл./подготовл.

Remarks

Степень защиты по IEC 60529 или ISO 20653, только в свинченном или вставленном состоянии с ответной частью.

Electrical data

Рабочее напряжение U _b	4.5...5.5 VDC
-----------------------------------	---------------

Environmental conditions

Степень защиты	IP40
----------------	------

Material

Материал контактов	Gold plated/Gold plated
Материал оболочки кабеля	TPE

Mechanical data

Длина кабеля L	2.00 m
Оболочка кабеля, цвет	черный

Connector Drawings

PIN	SIGNAL
1	RTS
4	GND
5	RX
6	TX
7	Vcc / Vcc-conn.
10	CTS

NOTE: all the other pins are not connected

10 PINS MALE TEL. CONN.



PIN	SIGNAL
2	TX
3	RX
5	GND
7	CTS
8	RTS
9	Vcc-conn.

NOTE: all the other pins are not connected
 connector's housing is connected to cable's shield

9 PINS FEMALE CONN. DE9S

