



Basic features

Application	Pneumatic cylinder with tie rods Cylinder diameter 3.25" to 4.0"
Basic standard	Dimension tolerances: DIN ISO 2768 m
Principle of operation	BMF mounting bracket
Scope of delivery	Fastening screw Mounting bracket Offset screwdriver
Style	Mounting bracket
Use	for magnetic sensors BMF 305

Environmental conditions

Ambient temperature	-40...85 °C
----------------------------	-------------

Material

Housing material	Aluminum
Material	Aluminum

Mechanical data

Dimension	Ø 19 x 4.83 mm
Mounting, holder	Threaded pin ISO 4027 M3x10-A2 Offset screwdriver ISO 2936 1.5 (2x)
Sensor attachment	Cylinder head screw DIN 7984 M3x6-A2 offset screwdriver ISO 2936 2.0
Tightening torque	1.5 Nm
Tightening torque clamping screw	1.5 Nm