



Basic features

Principle of operation Cams (inductive)

Material

Housing material Steel, Bronzed
 PA 6.6, Fiberglass

Material sensing surface Steel

Surface protection Bronzed

Mechanical data

Clamping system Expansion clamp

Foot shape for U-slot

Foot width 6.00 mm

Height above cam tray 12.00 mm

Switching surface, length (L) 30 mm

Mechanical Accessories
BEN 516-14-30
Order Code: **BEN0017**

BALLUFF

Use for cam tray
BNL 5307-160-...
BNL 5307-120-...
BNL 5304-160-...
BNL 5304-120-...

Use for switch position spacing 12 mm
16 mm
Width of switching area 10.00 mm