



- | | | | |
|-------------------|-------------------------|----------------------------|----------------------------|
| 1 Mic-In | 6 GPIO | 11 Power Connector 8-36VDC | 16 10/100/1000Mbit network |
| 2 Ear-Out | 7 RS485/COM4 switchable | 12 WIFI Connector | 17 10/100/1000Mbit network |
| 3 S/PDIF | 8 RS485/COM3 switchable | 13 COM1, RS232/RS485 | 18 HDMI connector |
| 4 TOS Link S/PDIF | 9 COM2 | 14 2x USB 2.0 | 19 WIFI Connector |
| 5 VGA | | 15 2x USB 3.0 | 20 On/Off Button |



Basic features

Approval/Conformity	CE EAC WEEE
Scope of delivery	12V/32W power supply WLAN antenna VESA pedestal USB-Stick with device driver
Short description	Touchpanel PC
Use	Accessories for SmartCamera

Environmental conditions

Ambient temperature	10...40 °C
Storage temperature	0...50 °C

Functional Characteristics

Supported operating systems	Windows 10 (32/64 bit)
------------------------------------	------------------------

Functional safety

MTTF (40 °C)	5 a
---------------------	-----

Material

Housing material	Glass Aluminum, black
-------------------------	--------------------------

Mechanical data

Dimension	310 x 56 x 240 mm
IP rating (front housing)	IP65
Mounting	VESA 100 mm
Weight	2150 g