

Basic features

Approval/Conformity	FDA compliant
	EAC
	Ecolab
	WEEE

Environmental conditions

Cable temperature, fixed routing	-50...105 °C
Cable temperature, flexible routing	-25...105 °C
IP rating	IP69K/IP69K

Electrical connection

Bending radius min., fixed cable	5 x D
Bending radius min., flexible cable	10 x D
Cable	TPE-V gray, 20 m
Cable diameter D	8.50 mm ±0.3 mm
Conductor cross-section	1.5 mm ²
Connection 1	7/8"-Female, straight, 4-pin
Connection 2	7/8"-Male, straight, 4-pin
Number of conductors	4
System	Molded/Molded

Material

Cable jacket, material	TPE-V
Material contact carrier	PP/PP
Material contacts	Brass/Brass
Material cover nut	Stainless steel (1.4404)/Stainless steel (1.4404)
Material grip	PP/PP

Electrical data

Cable rated voltage AC max.	600 V
Cable rated voltage DC max.	600 V
Operating voltage U_b	300 VDC / 300 VAC
Rated current (40 °C)	10.0 A


Mechanical data

Cable jacket, color	gray
Cable length L	20.00 m
Tightening torque pigtail	1.5 Nm/1.5 Nm


Remarks

Halogen-free per DIN VDE 0472 Part 815
 Halogen-free acc. to IEC 60754-1
 LABS-free
 Enclosure rating per IEC 60529 or 20653, only in screwed state with the associated mating piece.

Connector Drawings



II
PIN 1: brown
PIN 2: white
PIN 3: blue
PIN 4: black



I
PIN 1: brown
PIN 2: white
PIN 3: blue
PIN 4: black

Wiring Diagrams

