



## Basic features

<b>Additional features</b>	variable aperture
<b>Use</b>	for industrial cameras BVS CA-.. 12 MP
<b>Version</b>	C-Mount

## Material

<b>Housing material</b>	Aluminum, black anodized
<b>Material sensing surface</b>	Glass, polished

## Mechanical data

<b>Angle of view, horizontal</b>	83.5 °
<b>Angle of view, vertical</b>	66.7 °
<b>Dimension</b>	Ø 80 x 101.9 mm
<b>Filter thread size</b>	M77x0.5
<b>Mounting</b>	Screws
<b>Weight</b>	490 g

## Optical features

<b>Focal length</b>	8 mm
---------------------	------

## Range/Distance

<b>Minimum object distance (MOD)</b>	300 mm
--------------------------------------	--------

## Remarks

Angle of view refers to a sensor size of 1/1.1"