



**Basic features**

<b>Component</b>	Linear cam
<b>Per DIN 69639</b>	yes
<b>Principle of operation</b>	Cams (mechanical)

**Material**

<b>Material sensing surface</b>	Steel
<b>Surface</b>	Bronzed
<b>Surface hardened</b>	HRC 63±2

**Mechanical data**

<b>Clamping system</b>	Compression clamp
<b>Fine-adjustable</b>	no
<b>Foot shape for</b>	U-slot
<b>Foot width</b>	5.90 mm
<b>Height above cam tray</b>	12.60 mm
<b>Switching surface, length (L)</b>	10 mm
<b>Use for cam tray</b>	BNL 5307-160-... BNL 5307-120-... BNL 5304-160-... BNL 5304-120-...
<b>Use for switch position spacing</b>	16 mm 12 mm
<b>Width of switching area</b>	11.00 mm
<b>Working principle</b>	Mechanical