




1) Optical axis, 2) Sn, 3) Output function, 4) Operating voltage



Basic features

Approval/Conformity	CE cULus EAC WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Photoelectric sensor
Reference emitter	BOS 18M-XT-LS10-...
Series	18M
Style	Cylinder Straight optics

Display/Operation

Adjuster	Potentiometer 270°
Display	Output function- LED yellow LED green: Power
Setting	Sensitivity (Sn)

Electrical connection

Connection	Connector, M12x1-Male, 4-pin
Polarity reversal protected	yes
Short-circuit protection	yes

Electrical data

No-load current I_0 max. at U_e	35 mA
Operating voltage U_b	10...30 VDC
Protection class	II
Rated insulation voltage U_i	75 V DC
Rated operating current I_e	100 mA
Rated operating voltage U_e DC	24 V
Ripple max. (% of U_e)	8 %
Switching frequency	1500 Hz
Turn-off delay t_{off} max.	0.33 ms
Turn-on delay t_{on} max.	0.33 ms
Voltage drop U_d max. at I_e	2 V

Environmental conditions

Ambient temperature	-10...50 °C
EN 60068-2-27, Shock	Half-sinus, 50 gn, 500 ms, 3x3
EN 60068-2-6, Vibration	10...55 Hz, amplitude 0.5 mm, 3x30 min
IP rating	IP67

Functional safety

MTTF (40 °C)	455 a
--------------	-------

Interface

Switching output	PNP normally closed (NC) PNP normally open (NO) Pins 4-2
------------------	---

Material

Housing material	Brass, nickel-plated
Material sensing surface	PMMA
Surface protection	nickel-plated

Mechanical data

Dimension	Ø 18 x 81.5 mm
Mounting part	Nut M18x1
Tightening torque max.	22 Nm

Optical features

Ambient light max.	5000 Lux
Light type	Red light
Principle of optical operation	Through-beam sensor (receiver)
Switching function, optical	Light-on dark-on

Range/Distance

Range	0...60 m
Rated operating distance Sn	60 m, Adjustable

Remarks


Order accessories separately.
For additional information, refer to user's guide.
Actuation object (target): gray card, 200 x 200, lateral approach.
For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings



Wiring Diagrams (Schematic)



Opto Symbols

