



1) closed, 2) open

## Basic features

<b>Additional features</b>	Weld immune
<b>Principle of operation</b>	Clamp holder
<b>Scope of delivery</b>	Clamp holder (1x) Nut DIN 1763-M24x1.5 (2x)
<b>Use</b>	For M18 sensors

## Material

<b>Material</b>	Stainless steel
<b>Surface protection</b>	PTFE coated

## Mechanical data

<b>Dimension</b>	Ø 30 x 58 mm
<b>Mounting part</b>	Clamps
<b>Tightening torque</b>	15 Nm

## Environmental conditions

<b>Ambient temperature</b>	-25...70 °C
----------------------------	-------------

## Remarks

For proximity switches with mounting length 55 mm and longer.  
 The clamp holder was designed to retain size M18 proximity switches.  
 The holder is suitable for use in welding environments.