

1) Reference edge, 2) Sealing ring, 3) Function indicator FC, 4) Mark. Safety switch position



Basic features

Approval/Conformity	CE CCC WEEE
Basic standard	IEC 60947-5-1
Operating principle	1-2. Switch position: Mechanical with forced opening
Version	

Display/Operation

Function indicator	1-2. Switch position: FC - 6...24 V
--------------------	-------------------------------------

Electrical connection

Connection	M12x1-Flange male, 5-pin
Connection type	1. Switch position: Connector

Electrical data

Continuous current	1-2. Switch position: 4 A
Rated operating voltage Ue	1-2. Switch position: 24 V DC
Switching function mechanical	Single-pin changeover Forced-opening
Switching rate	1-2. Switch position: 200/min

Environmental conditions

Ambient temperature	-5...85 °C
IP rating	IP67

Functional safety

B10d (EN ISO 13849-1)	BSE 64: 10 mil. switching cycles
-----------------------	----------------------------------

Material

Housing material	Aluminium, Anodized
Housing material, surface protection	Anodized
Material contacts	1-2. Switch position: Silver
Plunger material	1-2. Switch position: 1.4034 stainless steel


Mechanical data

Approach direction	longitudinal, parallel to attachment surface
Approach speed	1-2. Switch position: 60 m/min
Distance cam - reference edge	1-2. Switch position: 2.50...2.80 mm
Flange, feed-through	1 threaded exit M16
Installation	Vertical
Life expectancy mechanical	1-2. Switch position: 10 mil. switching operations
Number of switching positions	2x Roller Mechanical
Plunger style	1-2nd switch position: Roller 1-2nd switch position: Roller
Switch actuation force	1-2. Switch position: 8 N
Switching element	1-2. Switch position: BSE 64

Range/Distance

Repeatability	1-2. Switch position: ±0.05 mm
---------------	--------------------------------

Connector Drawings



View of connector side

Wiring Diagrams (Schematic)

