




1) Reference edge, 2) Mark. Safety switch position, 3) Anti-crystallization plunger



Basic features

Approval/Conformity	CE CCC WEEE
Basic standard	IEC 60947-5-1
Operating principle	1. Switch position: Mechanical
Version	with forced opening

Display/Operation

Function indicator	1. Switch position: None
--------------------	--------------------------

Electrical connection

Connection type	1. Switch position: Screw terminal
-----------------	------------------------------------

Electrical data

Continuous current	1. Switch position: 5 A
Rated operating voltage U _e	1. Switch position: 250 V AC
Switching function mechanical	Single-pin changeover Forced-opening
Switching rate	1. Switch position: 200/min

Environmental conditions

Ambient temperature	-5...85 °C
IP rating	IP67

Functional safety

B10d (EN ISO 13849-1)	BSE 64: 10 mil. switching cycles
-----------------------	----------------------------------

Material

Housing material	Aluminium, Anodized
Housing material, surface protection	Anodized
Material contacts	1. Switch position: Silver
Plunger material	1. Switch position: 1.4034 stainless steel

Mechanical data

Approach direction	longitudinal, parallel to attachment surface
Approach speed	1. Switch position: 10 m/min
Dimension	42 x 47 x 22 mm
Distance cam - reference edge	1. Switch position: 2.50...2.80 mm
Flange, feed-through	None
Life expectancy mechanical	1. Switch position: 10 mil. switching operations
Number of switching positions	E-chisel Mechanical
Plunger spacing 1st switch position	11 mm
Plunger style	1st switch position: E-Chisel 1st switch position: E-Chisel
Switch actuation force	1. Switch position: 8 N
Switching element	1. Switch position: BSE 64

Range/Distance

Repeatability	1. Switch position: ±0.02 mm
---------------	------------------------------

Wiring Diagrams (Schematic)

