

CE  EAC 

Current consumption max. at 24 V DC	150 mA
Error signal Ia rising	≥ 20.4 mA
Error signal Ua falling	≤ 0 V
Error signal Ua rising	≥ 10.2 V
Galvanic isolation	yes
Inrush current	≤ 3 A/0.5 ms
Operating voltage Ub	20...28 VDC
Output signal adjustable	no
Overvoltage protection	Ub up to 28 V
Voltage-proof up to (GND to housing)	500 V DC

Ambient temperature	-40...+85 °C
EN 55016-2-3, Radiation	Industrial areas
EN 60068-2-27, Continuous shock	100 g, 2 ms
EN 60068-2-27, Shock	100 g, 6 ms
EN 60068-2-6, Vibration	12 g, 10...2000 Hz
EN 61000-4-2, ESD	Severity Level 3
EN 61000-4-3, RFI	Severity Level 3
EN 61000-4-4, Burst	Severity Level 3
EN 61000-4-5, Surge	Severity Level 2
EN 61000-4-6, High-frequency fields	Severity Level 3
EN 61000-4-8 Magnetic fields	Severity Level 4
IP rating	IP67, with connector
Relative humidity	≤ 90 %, non-condensing
Storage temperature	-40...+100 °C
Temperature coefficient typ.	≤ 35 ppm/K at 50% of nominal stroke 500mm

MTTF (40 °C) 77 a

Analog output Analog, current 4...20 mA

Material

Cover material	Aluminium, Die-cast, nickel plated
Housing material	Aluminium, Anodized
Housing material, surface protection	Anodized


Mechanical data

Mounting part	Mounting clamps
Null point	73.0 mm
Overall Length	196 mm

Range/Distance

Measuring length	55 mm
Non-linearity max.	$\pm 100 \mu\text{m}$
Repeat accuracy	$\leq \pm 0.2 \mu\text{A}$
Repeatability	$\leq 4 \mu\text{m}$
Resolution	$\leq 0.2 \mu\text{A}$
Sampling rate, length-dependent	1 kHz, standard

Connector Drawings



Wiring Diagrams (Schematic)

Pin	
1	4...20 mA
2	GND output
3	NC
4	NC
5	NC
6	GND
7	+24 V DC
8	NC