


1) not included in scope of delivery, 2) Non-usable area, 3) Nominal length = Measuring length, 10) Null point, 11) Installation length



## Basic features

|                                   |                            |
|-----------------------------------|----------------------------|
| Approval/Conformity               | CE<br>cULus<br>EAC<br>WEEE |
| Magnets, number (factory setting) | 1                          |
| Magnets, number max.              | 1                          |

## Electrical connection

|                                     |                            |
|-------------------------------------|----------------------------|
| Bending radius min., fixed cable    | 5 x D                      |
| Bending radius min., flexible cable | 15 x D                     |
| Cable diameter D                    | 6...6.7 mm                 |
| Cable length L                      | 2 m, drag chain compatible |
| Connection                          | Cable, 2.00 m, PUR         |
| Connection version                  | axial                      |
| Polarity reversal protected         | Ub up to 28 V              |

## Electrical data

|                                      |               |
|--------------------------------------|---------------|
| Current consumption max. at 24 V DC  | 150 mA        |
| Error signal Ia rising               | ≥ 20.4 mA     |
| Error signal Ua falling              | ≤ 0 V         |
| Error signal Ua rising               | ≥ 10.2 V      |
| Galvanic isolation                   | yes           |
| Inrush current                       | ≤ 3 A/0.5 ms  |
| Operating voltage Ub                 | 20...28 VDC   |
| Output signal adjustable             | no            |
| Overvoltage protection               | Ub up to 28 V |
| Voltage-proof up to (GND to housing) | 500 V DC      |

## Environmental conditions

|                                     |                                           |
|-------------------------------------|-------------------------------------------|
| Ambient temperature                 | -40...85 °C                               |
| Cable temperature, fixed routing    | -40...90 °C                               |
| Cable temperature, flexible routing | -5...90 °C                                |
| EN 55016-2-3, Radiation             | Industrial areas                          |
| EN 60068-2-27, Continuous shock     | 100 g, 2 ms                               |
| EN 60068-2-27, Shock                | 100 g, 6 ms                               |
| EN 60068-2-6, Vibration             | 12 g, 10...2000 Hz                        |
| EN 61000-4-2, ESD                   | Severity Level 3                          |
| EN 61000-4-3, RFI                   | Severity Level 3                          |
| EN 61000-4-4, Burst                 | Severity Level 3                          |
| EN 61000-4-5, Surge                 | Severity Level 2                          |
| EN 61000-4-6, High-frequency fields | Severity Level 3                          |
| EN 61000-4-8 Magnetic fields        | Severity Level 4                          |
| IP rating                           | IP67                                      |
| Relative humidity                   | ≤ 90 %, non-condensing                    |
| Storage temperature                 | -40...100 °C                              |
| Temperature coefficient typ.        | ≤ 35 ppm/K at 50% of nominal stroke 500mm |

## Functional safety

|              |      |
|--------------|------|
| MTTF (40 °C) | 77 a |
|--------------|------|

## Interface

|               |                           |
|---------------|---------------------------|
| Analog output | Analog, current 0...20 mA |
|---------------|---------------------------|

Material

|                                      |                                    |
|--------------------------------------|------------------------------------|
| Cable flame-resistant                | IEC 60332-1                        |
| Cable jacket, material               | PUR                                |
| Cover material                       | Aluminium, Die-cast, nickel plated |
| Housing material                     | Aluminium, Anodized                |
| Housing material, surface protection | Anodized                           |

Mechanical data

|                |                 |
|----------------|-----------------|
| Mounting part  | Mounting clamps |
| Null point     | 73.0 mm         |
| Overall Length | 206 mm          |

Range/Distance

|                                 |                 |
|---------------------------------|-----------------|
| Measuring length                | 60 mm           |
| Non-linearity max.              | ±100 µm         |
| Repeat accuracy                 | ≤ ± 0.2 µA      |
| Repeatability                   | ≤4 µm           |
| Resolution                      | ≤ 0.2 µA        |
| Sampling rate, length-dependent | 1 kHz, standard |

Wiring Diagrams (Schematic)

| colour |            |
|--------|------------|
| YE     | 0...20 mA  |
| GY     | GND output |
| PK     | NC         |
| GN     | NC         |
| BU     | GND        |
| BN     | +24 V DC   |
| WH     | NC         |