



Basic features

Basic standard	IEC 60947-5-2
Reference base unit	BFB 75K-001-..
Use	for fiber optic base units BFB
Version	5x15, 90° light grid

Environmental conditions

Ambient temperature	-55...70 °C
Ambient temperature connection area	Acc. to fiber optic sensor
Protection degree	IP65

Material

Active surface, fiber arrangement	Row
Fiber type material	PMMA
Housing material	Brass, nickel plated
Material jacket	PE
Surface protection	nickel plated

Mechanical data

Active surface, fibers	Ø 0.25 mm (16x)
Cable diameter D	2.20 mm
Cable length L	2 m
Cable, bending radius min.	25 mm
Cable, note	can be trimmed
Connection type	Cable, 2.00 m, PE
Dimension	5 x 15 x 15 mm
Fiber optic cable, structure	Fiber bundle in plastic jacket
Length B min., without bending	20.00 mm
Mounting	Screw M3
Tensile load max. at 20 °C	6 N (max. 3s)

Range/Distance

Range	400 mm
Rated operating distance S_n	400 mm
Real switching distance s_r	400 mm

Remarks

The cutting tool is included in the scope of delivery order other accessories separately.

Cut cable to length: use suitable cutting tool. Make a single cut, vertical to cable axis. The cut quality can affect the switching distance.

Route fiber optic cable so that no excessive tensile, compression or torsional forces are permitted. Observe permissible bending radiuses. Installation may affect the switching distance.

Opto Symbols

