

1) Sensing surface, 2) Sensor 1



### Basic features

Approval/Conformity	cULus CE WEEE EAC
Basic standard	IEC 60947-5-2
Not incl. in scope of delivery	Mounting bracket, e.g. BMF 305-HW-17
Principle of operation	Magnetic field sensor

### Display/Operation

Function indicator	yes
--------------------	-----

### Electrical connection

Cable	PUR, 0.3 m
Cable diameter D	3.00 mm
Connection	M8x1-Male, 4-pin
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

### Electrical data

Assured switching field strength Ha	2 kA/m
Hysteresis H max. (% of Hn)	45 %
Load capacitance max. at Ue	1 µF
No-load current Io max., undamped	10 mA
Operating voltage Ub	10...30 VDC
Output resistance Ra	Open drain
Rated insulation voltage Ui	75 V DC
Rated operating current Ie	200 mA
Rated operating voltage Ue DC	24 V
Rated short circuit current	100 A
Rated switch field strength Hn	1.2 kA/m
Residual current Ir max.	80 µA
Ripple max. (% of Ue)	15 %
Switching frequency	10000 Hz
Turn-off delay toff max.	0.05 ms
Turn-on delay ton max.	0.05 ms
Utilization category	DC -13
Voltage drop static max.	3.1 V

### Environmental conditions

Ambient temperature	-25...85 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
ESD	4A(15kV)
Emission	Group 1, Class B
IP rating	IP67

Magnetic Sensors  
**BMF 305K-PS-C-2-SA95-S75-00,3**  
Order Code: BMF0060

**BALLUFF**

**Functional safety**

MTTF (40 °C) 330 a

**Material**

Housing material LCP  
Jacket material PUR  
Material sensing surface PU

**Mechanical data**

Dimension 33.5 x 5 x 10.5 mm

**Output/Interface**

Switching output PNP normally open (NO)

**Range/Distance**

Temp. drift max. (% of Hn) 0.3 %

**Remarks**


The sensor is functional again after the overload has been eliminated.  
For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

**Connector Drawings**



**Wiring Diagrams**



Technical Drawings

