

4MT5
(CYJV CABLE ASSEMBLY)



Basic features

| | |
|---------------------|----------------------------|
| Approval/Conformity | CE cULus EAC WEEE |
|---------------------|----------------------------|

Electrical connection

| | |
|-------------------------------------|---------------------------------------|
| Bending radius min., fixed cable | 5 x D |
| Bending radius min., flexible cable | 10 x D |
| Cable | PVC gray, 5 m, Drag chain compatible |
| Cable diameter D | 4.80 mm ±0.15 mm |
| Cable, bending cycles min. | 2 million |
| Conductor cross-section | 0.34 mm ² |
| Connection 1 | M8x1-Female, straight, 4-pin, A-coded |
| Connection 2 | M12x1-Male, straight, 4-pin, A-coded |
| Number of conductors | 4 |
| System | Molded/Molded |

Electrical data

| | |
|-----------------------|-----------------|
| Operating voltage Ub | 60 VDC / 60 VAC |
| Rated current (40 °C) | 4.0 A |

Environmental conditions

| | |
|---|-------------------------------|
| Cable temperature UL max., fixed routing | 80 °C |
| Cable temperature UL max., flexible routing | 80 °C |
| Cable temperature, drag chain | -5...60 °C |
| Cable temperature, fixed routing | -40...105 °C |
| Cable temperature, flexible routing | 5...105 °C |
| Protection degree | IP67, IP69K/IP67, IP68, IP69K |

Material

| | |
|--------------------------|--|
| Cable jacket, material | PVC |
| Material contact carrier | PUR/PUR |
| Material contacts | Bronze/Brass |
| Material cover nut | Die-cast zinc or nickel plated brass/Die-cast zinc |
| Material grip | PUR/PUR |

Mechanical data

| | |
|---|-----------------------|
| Acceleration max., drag chain | 5 m/s ² |
| Cable jacket, color | gray |
| Cable length L | 5.00 m |
| Cable properties | Drag chain compatible |
| Horizontal travel permitted, drag chain | 5 m |
| Tightening torque pigtail | 0.4 Nm/0.6 Nm |
| Traverse speed max., drag chain | 200 m/min |
| Vertical travel permitted, drag chain | 2 m |


Output/Interface

| | |
|------------------|---------------|
| Switching output | Complementary |
|------------------|---------------|

Remarks

Cable construction acc. to UL-AWM Style 2517
Silicone-free
Flame-retarding acc. to IEC 60332-2
Enclosure rating per IEC 60529 or 20653, only in screwed state with the associated mating piece.

Connector Drawings



Wiring Diagrams

