

4MT5  
(CYJV CABLE ASSEMBLY)



## Basic features

Approval/Conformity	CE cULus EAC WEEE
---------------------	----------------------------

## Electrical connection

Bending radius min., fixed cable	7.5 x D
Bending radius min., flexible cable	10 x D
Cable	PUR black, 5 m, Drag chain compatible
Cable diameter D	8.70 mm ±0.20 mm
Cable, bending cycles min.	5 million
Conductor cross-section	1.5 mm <sup>2</sup>
Connection	7/8"-Female, right-angle, 5-pin
Connector configuration	right-angle
Number of conductors	5
Number of pins	5
System	Molded

## Electrical data

Operating voltage $U_b$	300 VDC / 300 VAC
Rated current (40 °C)	9.0 A

## Remarks

Cable construction acc. to UL-AWM Style 20234  
 Halogen-free  
 Silicone-free  
 Flame-retarding  
 Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

## Environmental conditions

Cable temperature, fixed routing	-50...80 °C
Cable temperature, flexible routing	-20...80 °C
IP rating	IP67, IP68

## Material

Cable jacket, material	PUR
Material contact carrier	PUR
Material contacts	Brass
Material cover nut	Die-cast zinc
Material grip	PUR


## Mechanical data

Acceleration max., drag chain	5 m/s <sup>2</sup>
Cable jacket, color	black
Cable length L	5.00 m
Cable properties	Drag chain compatible
Horizontal travel permitted, drag chain	20 m
Tightening torque pigtail	1.5 Nm
Traverse speed max., drag chain	300 m/min

## Output/Interface

Switching output	Complementary
------------------	---------------

## Connector Drawings



- PIN 1: black
- PIN 2: blue
- PIN 3: green/yellow
- PIN 4: brown
- PIN 5: white

## Wiring Diagrams

