



1) Reference edge, 2) Anti-crystallization plunger



### Basic features

Approval/Conformity	CE WEEE
Basic standard	IEC 60947-5-1
Operating principle	1-2. Switch position: Mechanical
Version	Snap contact

### Display/Operation

Function indicator	1-2. Switch position: None
--------------------	----------------------------

### Electrical connection

Connection type	1-2. Switch position: Screw terminal
-----------------	--------------------------------------

### Electrical data

Continuous current	1-2. Switch position: 5 A
Rated operating voltage U <sub>e</sub>	1-2. Switch position: 250 V AC
Switching function mechanical	Single-pin changeover
Switching rate	1-2. Switch position: 200/min

### Environmental conditions

Ambient temperature	-5...85 °C
Protection degree	IP67

### Functional safety

B10d (EN ISO 13849-1)	BSE 70.1: 10 mil. Switching operations
-----------------------	--

### Material

Housing material	Aluminum, Anodized
Housing material, surface protection	Anodized
Material contacts	1-2. Switch position: Silver
Plunger material	1-2. Switch position: Stainless steel (1.4034)

### Mechanical data

Approach direction	longitudinal, parallel to attachment surface
Approach speed	1-2. Switch position: 10 m/min
Dimension	40 x 34 x 48 mm
Distance cam - reference edge	1-2. Switch position: 2.30...2.80 mm
Flange, feed-through	None
Installation	Vertical
Life expectancy mechanical	1-2. Switch position: 10 million Switching operations
Number of switching positions	2x E-Chisel
Plunger spacing 1st switch position	13 mm
Plunger style	1-2nd switch position: E-chisel
Switch actuation force	1-2. Switch position: 8 N
Switching element	1-2. Switch position: BSE 70.1

### Range/Distance

Reproducibility	1-2. Switch position: ±0.02 mm
Switch position spacing	8 mm

## Wiring Diagrams

