



1) Reference edge, 2) 1st pos.



### Basic features

Approval/Conformity	CE WEEE
Basic standard	IEC 60947-5-1
Operating principle	1-5. Switch position: Mechanical
Version	Snap contact

### Display/Operation

Function indicator	1-5. Switch position: None
--------------------	----------------------------

### Electrical connection

Connection type	1-5. Switch position: Screw terminal
-----------------	--------------------------------------

### Electrical data

Continuous current	1-5. Switch position: 6 A
Rated operating voltage $U_e$	1-5. Switch position: 250 V AC
Switching function mechanical	Double-interrupting galvanically isolated One NO and one NC Dual changeover
Switching rate	1-5. Switch position: 300/min

### Environmental conditions

Ambient temperature	-5...85 °C
Protection degree	IP67

### Functional safety

B10d (EN ISO 13849-1)	BSE 30.0: 30 mil. Switching operations
-----------------------	----------------------------------------

### Material

Housing material	Aluminum, Anodized
Housing material, surface protection	Anodized
Material contacts	1-5. Switch position: Silver, gold plated
Plunger material	1-5. Switch position: Stainless steel (1.4034)

### Mechanical data

Approach direction	Vertical to mounting surface
Approach speed	1-5. Switch position: 40 m/min
Dimension	116 x 90 x 77 mm
Distance cam - reference edge	1-5. Switch position: 2.50...3.00 mm
Flange, feed-through	1 threaded exit M25
Installation	Vertical
Life expectancy mechanical	1-5. Switch position: 30 million Switching operations
Number of switching positions	5x Chisel
Plunger spacing 1st switch position	50 mm
Plunger style	1-5. switch position: Chisel
Switch actuation force	1-5. Switch position: 20 N
Switching element	1-5. Switch position: BSE 30.0

Range/Distance

Reproducibility  
Switch position spacing

1-5. Switch position:  $\pm 0.002$  mm  
12 mm

## Wiring Diagrams

BSE 30.0

