



1) Reference edge, 2) Sensing surface, 3) Function indicator FD/FE/LL, 4) 1st pos.



Basic features

Approval/Conformity	CE WEEE EAC
Basic standard	IEC 60947-5-2
Operating principle	1-6. Switch position: Inductive
Version	Inductive

Display/Operation

Function indicator	1-6. Switch position: Optical fiber
--------------------	-------------------------------------

Electrical connection

Connection type	1-6. Switch position: Screw terminal
Electrical version	3-/4-wire

Electrical data

Continuous current	1-6. Switch position: 0.13 A
Rated operating voltage U _e	1-6. Switch position: 24 V DC

Environmental conditions

Ambient temperature	-25...70 °C
IP rating	IP67

Functional safety

MTTF (40 °C)	BES 517-142-Y: 1680 a
--------------	-----------------------

Material

Housing material	Aluminum, Anodized
Housing material, surface protection	Anodized

Mechanical data

Distance cam - active surface	1-6. Switch position: 0...4.05 mm
Flange, feed-through	1 threaded exit M25
Installation	parallel
Switching element	1-6. Switch position: BES 517-142-Y

Output/Interface

Switching output	PNP complementary
------------------	-------------------

Range/Distance

Assured operating distance S _a	1-6. Switch position: 4 mm
Range	5 mm
Rated operating distance S _n	1-6. Switch position: 5.0 mm

Wiring Diagrams

