

1) Reference edge, 2) 1st pos., 3) Mark. Safety switch position



Basic features

Approval/Conformity	CE WEEE
Basic standard	IEC 60947-5-1
Operating principle	1-5. Switch position: Mechanical
Version	Safety EN 60204-1

Display/Operation

Function indicator	1-5. Switch position: None
--------------------	----------------------------

Electrical connection

Connection type	1-5. Switch position: Screw terminal
-----------------	--------------------------------------

Electrical data

Continuous current	1-5. Switch position: 6 A
Rated operating voltage Ue	1-5. Switch position: 250 V AC
Switching rate	1-5. Switch position: 300/min

Environmental conditions

Ambient temperature	-5...85 °C
IP rating	IP67

Functional safety

B10d (EN ISO 13849-1)	BSE 30.0: 30 mil. Switching operations BSE 61: 30 mil. Switching operations
-----------------------	--

Material

Housing material	Aluminum, Anodized
Housing material, surface protection	Anodized
Material contacts	1-2. Switch position: Silver 3-5. Switch position: Silver, gold plated
Plunger material	1-5. Switch position: Stainless steel (1.4034)

Mechanical data


Approach direction	Vertical to mounting surface
Approach speed	1-5. Switch position: 60 m/min
Distance cam - reference edge	1-5. Switch position: 2.50...3.00 mm
Flange, feed-through	1 threaded exit M25
Installation	Horizontal
Life expectancy mechanical	1-5. Switch position: 30 million Switching operations
Number of switching positions	5x Roller
Plunger style	1-5. switch position: Roller
Switch actuation force	1-2. Switch position: 15 N 3-5. Switch position: 20 N
Switching element	1-2. Switch position: BSE 61 3-5. Switch position: BSE 30.0

Range/Distance

Reproducibility	1-5. Switch position: ±0.01 mm
-----------------	--------------------------------

Wiring Diagrams

BSE 61



BSE 30.0

