



1) O-Ring with thrust ring



### Basic features

Approval/Conformity	CE EAC WEEE
Basic standard	IEC 60947-5-2
Thrust ring, part number	505953

### Display/Operation

Function indicator	no
Power indicator	no

### Electrical connection

Connection	M12x1-Male, 4-pin, A-coded
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

### Electrical data

Load capacitance max. at $U_e$	0.5 $\mu$ F
Min. operating current $I_m$	0 mA
No-load current $I_o$ max., damped	10 mA
No-load current $I_o$ max., undamped	1 mA
Operating voltage $U_b$	10...30 VDC
Output resistance $R_a$	33.0 kOhm + D
Rated insulation voltage $U_i$	75 V DC
Rated operating current $I_e$	200 mA
Rated operating voltage $U_e$ DC	24 V
Rated short circuit current	100 A
Ready delay $t_v$ max.	10 ms
Residual current $I_r$ max.	10 $\mu$ A
Ripple max. (% of $U_e$ )	15 %
Switching frequency	1000 Hz
Utilization category	DC -13
Voltage drop static max.	1.5 V

### Environmental conditions

Ambient temperature	-25...80 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
Protection degree	IP68

### Functional safety

MTTF (40 °C)	720 a
--------------	-------

**Inductive Sensors**  
**BES 516-300-S144-S4-D**  
**Order Code: BHS001N**



**Material**

Gasket, material	NBR 60-80
Housing material	Stainless steel
Material sensing surface	EP
Support ring material	PTFE

**Mechanical data**

Dimension	Ø 18 x 73 mm
Installation	for flush mounting
Mounting	M18x1
Pressure rating max.	350 bar
Pressure rating, note	oil pressure rated
Sealing ring, part number	703843
Sealing ring, size	11 x 1.8 mm
Size	M18x1
Tightening torque	40 Nm ±10 %

**Output/Interface**

Switching output	PNP normally open (NO)
------------------	------------------------

**Range/Distance**

Assured operating distance Sa	1.2 mm
Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance Sn	1.5 mm
Real switching distance sr	1.5 mm
Repeat accuracy max. (% of Sr)	5.0 %
Temperature drift max. (% of Sr)	10 %
Tolerance Sr	±10 %

**Remarks**

Installation Instructions 614804

The sensor is functional again after the overload has been eliminated.

For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

**Connector Drawings**



**Wiring Diagrams**

