



1) Reference edge, 2) Function indicator FD/FE/LL, 3) Sensing surface



### Basic features

<b>Approval/Conformity</b>	CE WEEE EAC
<b>Basic standard</b>	IEC 60947-5-2
<b>Operating principle</b>	1-3. Switch position: Inductive
<b>Version</b>	Inductive

### Display/Operation

<b>Function indicator</b>	1-3. Switch position: Optical fiber
---------------------------	-------------------------------------

### Electrical connection

<b>Connection type</b>	1-3. Switch position: Screw terminal
<b>Electrical version</b>	2-wire

### Electrical data

<b>Continuous current</b>	1-3. Switch position: 0.1 A
<b>Rated operating voltage Ue</b>	1-3. Switch position: 24 V DC

### Environmental conditions

<b>Ambient temperature</b>	-25...70 °C
<b>IP rating</b>	IP67

### Material

<b>Housing material</b>	Aluminum, Anodized
<b>Housing material, surface protection</b>	Anodized

### Mechanical data

<b>Distance cam - active surface</b>	1-3. Switch position: 0...1.62 mm
<b>Flange, feed-through</b>	None
<b>Installation</b>	Vertical
<b>Switching element</b>	1-3. Switch position: BES 517-560-H

### Range/Distance

<b>Assured operating distance Sa</b>	1-3. Switch position: 1.6 mm
<b>Range</b>	2 mm
<b>Rated operating distance Sn</b>	1-3. Switch position: 2.0 mm

## Wiring Diagrams

