

Basic features

Approval/Conformity	CE EAC WEEE
---------------------	-------------------

Electrical connection

Bending radius min., fixed cable	5 x D
Cable	PVC Shielded gray, 20.00 m
Cable diameter D	5.00 mm ±0.10 mm
Conductor cross-section	0.34 mm ²
Connection	M8x1-Female, right-angle, 3-pin, A-coded
Connector configuration	right-angle
Number of conductors	3
Number of pins	3
System	Molded

Electrical data

Operating voltage Ub	60 VDC / 60 VAC
Rated current (40 °C)	4.0 A

Remarks

Cable construction acc. to UL-AWM Style 2517
 Silicone-free
 Flame resistance acc. to FT1
 360° shield on cover nut
 Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

Environmental conditions

Cable temperature UL max., fixed routing	80 °C
Cable temperature, fixed routing	-20...105 °C
IP rating	IP67


Material

Cable jacket material, note	Shielded
Cable jacket, material	PVC
Cable shield	Copper braid, tin-plated
Material contact carrier	PUR
Material contacts	Bronze
Material cover nut	Brass nickel plated
Material grip	PUR

Mechanical data


Cable jacket, color	gray
Cable length L	20.00 m
Tightening torque pigtail	0.4 Nm

Connector Drawings



PIN 1: brown
PIN 3: blue
PIN 4: black

Wiring Diagrams



1) Shield on cover nut