



1) Sensing surface



IND. CONT. EQ.
 81U2
 Class 2 Type 1



Basic features

Approval/Conformity	cULus CE EAC WEEE
Basic standard	IEC 60947-5-2

Display/Operation

Function indicator	yes
Power indicator	no

Electrical connection

Cable diameter D	2.40 mm
Cable length L	2 m
Conductor cross-section	0.10 mm ²
Connection type	Cable, 2.00 m, PUR
Number of conductors	3
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Electrical data

Load capacitance max. at U _e	0.15 µF
Min. operating current I _m	0 mA
No-load current I _o max., damped	2 mA
No-load current I _o max., undamped	5 mA
Operating voltage U _b	10...30 VDC
Output resistance R _a	Open drain
Rated insulation voltage U _i	75 V DC
Rated operating current I _e	100 mA
Rated operating voltage U _e DC	24 V
Rated short circuit current	100 A
Ready delay t _v max.	25 ms
Residual current I _r max.	10 µA
Ripple max. (% of U _e)	10 %
Switching frequency	3500 Hz
Utilization category	DC -13
Voltage drop static max.	2 V

Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 g _n , 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
IP rating	IP67

Functional safety

MTTF (40 °C)	305 a
--------------	-------

Inductive Sensors
BES 516-3045-G-E4-C-PU-02
Order Code: BES00M7

BALLUFF

Material

Housing material	Stainless steel
Material jacket	PUR
Material sensing surface	PBT

Mechanical data

Dimension	Ø 3 x 27 mm
Installation	for flush mounting
Size	D3.0

Output/Interface

Switching output	PNP normally closed (NC)
------------------	--------------------------

Range/Distance

Assured operating distance Sa	0.8 mm
Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance Sn	1 mm
Real switching distance sr	1 mm
Repeat accuracy max. (% of Sr)	5.0 %
Switching distance marking	■
Temperature drift max. (% of Sr)	10 %
Tolerance Sr	±10 %

Remarks

EMC: Surge resistance
External protection circuit is required. Document 825345, Section 2.
The sensor is functional again after the overload has been eliminated.
The temperature drift can be below -15°C and above +60°C, up to 15% of Sr.
For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Wiring Diagrams

