



1) Sensing surface



### Basic features

|                     |                            |
|---------------------|----------------------------|
| Approval/Conformity | CE<br>cULus<br>EAC<br>WEEE |
| Basic standard      | IEC 60947-5-2              |

### Display/Operation

|                    |     |
|--------------------|-----|
| Function indicator | yes |
| Power indicator    | no  |

### Electrical connection

|                                   |                      |
|-----------------------------------|----------------------|
| Cable diameter D                  | 3.00 mm              |
| Cable length L                    | 2 m                  |
| Conductor cross-section           | 0.14 mm <sup>2</sup> |
| Connection type                   | Cable, 2.00 m, PVC   |
| Number of conductors              | 3                    |
| Polarity reversal protected       | yes                  |
| Protection against device mix-ups | yes                  |
| Short-circuit protection          | yes                  |

### Electrical data

|   |                |
|---|----------------|
| Load capacitance max. at Ue                   | 0.2 µF         |
| No-load current I <sub>0</sub> max., damped   | 10 mA          |
| No-load current I <sub>0</sub> max., undamped | 3 mA           |
| Operating voltage U <sub>b</sub>              | 10...30 VDC    |
| Output resistance R <sub>a</sub>              | Open collector |
| Rated insulation voltage U <sub>i</sub>       | 75 V DC        |
| Rated operating current I <sub>e</sub>        | 100 mA         |
| Rated operating voltage U <sub>e</sub> DC     | 24 V           |
| Rated short circuit current                   | 100 A          |
| Ready delay t <sub>v</sub> max.               | 15 ms          |
| Residual current I <sub>r</sub> max.          | 1 µA           |
| Ripple max. (% of U <sub>e</sub> )            | 15 %           |
| Switching frequency                           | 3000 Hz        |
| Utilization category                          | DC -12         |
| Voltage drop static max.                      | 2.5 V          |

### Environmental conditions

|                         |                                 |
|-------------------------|---------------------------------|
| Ambient temperature     | -25...70 °C                     |
| Contamination scale     | 3                               |
| EN 60068-2-27, Shock    | Half-sinus, 30 gn, 11 ms        |
| EN 60068-2-6, Vibration | 55 Hz, amplitude 1 mm, 3x30 min |
| Protection degree       | IP67                            |

### Functional safety

|              |       |
|--------------|-------|
| MTTF (40 °C) | 830 a |
|--------------|-------|

Inductive Sensors  
**BES R03KC-PSC30B-EV02**  
Order Code: BES01WU

**BALLUFF**

**Material**

|                          |                  |
|--------------------------|------------------|
| Housing material         | PA 6, GF30       |
| Material jacket          | PVC              |
| Material sensing surface | PA 6, GF30/black |

**Mechanical data**

|              |                    |
|--------------|--------------------|
| Dimension    | 30 x 10 x 6 mm     |
| Installation | for flush mounting |
| Size         | 30x10x6            |

**Output/Interface**

|                  |                        |
|------------------|------------------------|
| Switching output | PNP normally open (NO) |
|------------------|------------------------|

**Range/Distance**

|                                  |        |
|----------------------------------|--------|
| Assured operating distance Sa    | 2.4 mm |
| Hysteresis H max. (% of Sr)      | 15.0 % |
| Rated operating distance Sn      | 3 mm   |
| Real switching distance sr       | 3 mm   |
| Repeat accuracy max. (% of Sr)   | 5.0 %  |
| Temperature drift max. (% of Sr) | 10 %   |
| Tolerance Sr                     | ±10 %  |

**Remarks**

The sensor is functional again after the overload has been eliminated.  
For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

**Wiring Diagrams**

