



Basic features

Approval/Conformity	cULus CE EAC WEEE
Basic standard	IEC 60947-5-2
Trademark	Global

Display/Operation

Function indicator	yes
Power indicator	no

Electrical connection

Connection	M12x1-Male, 4-pin, A-coded
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Electrical data

Load capacitance max. at U_e	1 μ F
Min. operating current I_m	5 mA
Operating voltage U_b	10...36 VDC
Rated insulation voltage U_i	75 V DC
Rated operating current I_e	100 mA
Rated operating voltage U_e DC	24 V
Rated short circuit current	100 A
Ready delay t_v max.	50 ms
Residual current I_r max.	600 μ A
Ripple max. (% of U_e)	15 %
Switching frequency	1300 Hz
Utilization category	DC -13
Voltage drop static max.	5.3 V

Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
Protection degree	IP67

Functional safety

MTTF (40 °C)	315 a
--------------	-------

Material

Housing material	Brass
Material sensing surface	PA 12
Surface protection	Nickel-free coated

Mechanical data

Dimension	Ø 12 x 50 mm
Installation	for flush mounting
Size	M12x1
Tightening torque	15 Nm

Output/Interface

Switching output	non-polarized normally closed (NC)
------------------	------------------------------------

Range/Distance

Assured operating distance Sa	2.4 mm
Hysteresis H max. (% of Sr)	20.0 %
Rated operating distance Sn	3 mm
Real switching distance sr	3 mm
Repeat accuracy max. (% of Sr)	5.0 %
Switching distance marking	■ ■
Temperature drift max. (% of Sr)	10 %
Tolerance Sr	±10 %

Remarks

Specify maximum attainable switching frequency (not per IEC 60947-5-2)
 Flush: See installation instructions for inductive sensors with extended range 825357.
 The sensor is functional again after the overload has been eliminated.
 For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings



Wiring Diagrams

