

4MT5  
(CYJV CABLE ASSEMBLY)



## Basic features

Application	very good mechanical strength
Approval/Conformity	cULus EAC WEEE

## Electrical connection

Bending radius min., fixed cable	5 x D
Bending radius min., flexible cable	10 x D
Cable	PUR black, 2.00 m
Cable diameter D	5.10 mm ±0.20 mm
Conductor cross-section	0.34 mm <sup>2</sup>
Connection 1	7/8"-Female, straight, 4-pin
Connection 2	7/8"-Male, angled, 4-pin
Number of conductors	4
Protection jacket color	silver
System	Molded/Molded

## Electrical data

Operating voltage U <sub>b</sub>	300 VDC / 300 VAC
Rated current (40 °C)	4.0 A

## Remarks

Cable construction acc. to UL-AWM Style 20549  
 Halogen-free per DIN VDE 0472 Part 815  
 Flame resistance per UL FT2  
 Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

## Environmental conditions

Cable temperature UL max., fixed routing	80 °C
Cable temperature UL max., flexible routing	80 °C
Cable temperature, fixed routing	-50...90 °C
Cable temperature, flexible routing	-25...90 °C
Protection degree	IP65/IP65


## Material

Cable jacket, material	PUR
Jacket material	V2A
Material contact carrier	PUR/PUR
Material contacts	Brass/Brass
Material cover nut	Brass PTFE coated/Brass PTFE coated
Material grip	PUR, special/PUR, special

## Mechanical data

Cable jacket, color	black
Cable length L	2.00 m
Tightening torque pigtail	1.5 Nm/1.5 Nm

## Connector Drawings




II

PIN 1: brown

PIN 2: white

PIN 3: blue

PIN 4: black



I

PIN 1: brown

PIN 2: white

PIN 3: blue

PIN 4: black

## Wiring Diagrams

