

### Basic features

Approval/Conformity	CE cULus WEEE
---------------------	---------------------

### Electrical connection

Connection	M12x1-Male, 4-pin, A-coded
Electrical version	2-wire
Polarity reversal protected	yes
Short-circuit protection	yes

### Electrical data

Current draw max.	25 mA
Load cycles	100 million
Operating voltage U <sub>b</sub>	8...32 VDC
Protection class	III

### Environmental conditions

Ambient temperature	-25...85 °C
Compensation temperature	-25...85 °C
EN 60068-2-27, Shock	500 g, 1 ms
EN 60068-2-6, Vibration	10 g, 25...2000 Hz
Interference immunity	EN 61326-2-3: 2006
Media temperature	-40...125 °C
Noise emission	EN 61326-2-3: 2006
Protection degree	IP67
Storage temperature	-40...85 °C
Temperature coefficient typ.	≤ ±0.5 % FSO/10K

### Functional safety

MTTF (40 °C)	1388 a
--------------	--------

### Material

Connector housing, material	Nickel-plated brass
Gasket, material	Fluoroelastomer
Housing material	Stainless steel (1.4301)
Measuring cell, material	Ceramic Al <sub>2</sub> O <sub>3</sub>
Process connection material	Stainless steel (1.4301)

### Mechanical data

Process connection	G 1/4" with pulse protection
Pulse protection	Throttle screw 0.3 mm
Tightening torque max.	5 Nm
Weight	120.00 g


### Output/Interface

Analog output	Analog, current 4...20 mA
---------------	---------------------------

### Range/Distance

Accuracy	±0.5 % FSO BFSL
Burst pressure	750.00 bar
Long-term stability max.	0.3 % FSO/year
Measuring range	0...250 bar
Overload pressure	400 bar
Resolution	≤ 14 bits
Response time max.	10 ms
Sampling rate	1 ms

## Connector Drawings



## Wiring Diagrams

