

4MT5  
 (CYJV CABLE ASSEMBLY)  
 For Use in Class 2 Circuits Only



## Basic features

Application	Welding area
Approval/Conformity	CE cULus EAC WEEE

## Electrical connection

Bending radius min., fixed cable	7.5 x D
Bending radius min., flexible cable	15 x D
Cable	FEP welding spark resistant black, 2.00 m
Cable diameter D	4.10 mm ±0.30 mm
Conductor cross-section	0.34 mm <sup>2</sup>
Connection	M8x1-Female, Straight, 4-pin, A-coded
Connector configuration	Straight
Number of conductors	4
Number of pins	4
System	Molded

## Electrical data

Operating voltage Ub	60 VDC / 60 VAC
Rated current (40 °C)	4.0 A

## Remarks

Cable construction acc. to UL-AWM Style 2749  
 Maximum temperature at outer jacket from weld spatter/beads short-time 800°C.  
 Flame-retarding  
 Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

## Environmental conditions

Cable temperature, fixed routing	-100...200 °C
Protection degree	IP65

## Material

Cable jacket material, note	welding spark resistant
Cable jacket, material	FEP
Material contact carrier	PUR, special
Material contacts	Bronze
Material cover nut	Brass PTFE coated
Material grip	PUR, special


## Mechanical data

Cable jacket, color	black
Cable length L	2.00 m
Tightening torque pigtail	0.4 Nm

## Output/Interface

Switching output	Complementary
------------------	---------------

## Connector Drawings



PIN 1: brown  
PIN 2: white  
PIN 3: blue  
PIN 4: black

## Wiring Diagrams

