

**Basic features**

Approval/Conformity	CE cULus EAC WEEE
Basic standard	EN 61326-1
Measuring principle	MEMS

**Electrical connection**

Connection	M12x1
Polarity reversal protected	yes
Protection against device mix-ups	no
Short-circuit protection	yes

**Electrical data**

Current draw max.	25 mA
Load resistance min., analog output	20 kOhm
Operating voltage U <sub>b</sub>	12...30 VDC
Protection class	III
Rated operating voltage U <sub>e</sub> DC	24 V
Ready delay t <sub>v</sub> max.	1 s

**Environmental conditions**

Ambient temperature	-40...80 °C
Contamination scale	3
EN 60068-2-27, Shock	yes
EN 60068-2-6, Vibration	yes
IP rating	IP67
Relative humidity	95 %, non-condensing
Storage temperature	-40...85 °C

**Functional safety**

MTTF (40 °C)	121 a
--------------	-------

**Material**

Housing material	Plastic
------------------	---------

**Mechanical data**

Dimension	50 x 27 x 78 mm
Measuring axes	2
Mounting	Screws
Rotation direction	Clockwise
Weight	110.00 g

**Output/Interface**

Analog output	2x Analog, voltage 0...10 V
---------------	-----------------------------

**Range/Distance**


Accuracy	±0.12°
Resolution	≤ 0.01 °
Sampling rate	20 ms
Temperature drift max.	±0.1°/10 K

Remarks

Centering in a range of  $\pm 5^\circ$  from horizontal is possible  
For more information about MTTF and B10d see MTTF / B10d Certificate


Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings



- PIN 1: Y 0..10 V
- PIN 2: Vcc
- PIN 3: Int. use
- PIN 4: Int. use
- PIN 5: GND
- PIN 6: Centering
- PIN 7: 0..10 V
- PIN 8: Shield

Technical Drawings



Output signal measuring range

Help Views

