

## Basic features

Approval/Conformity	CE
	EAC
	WEEE

## Electrical connection

Bending radius min., fixed cable	5 x D
Bending radius min., flexible cable	10 x D
Cable	PVC gray, 1.00 m
Cable diameter D	5.00 mm ±0.20 mm
Conductor cross-section	0.50 mm <sup>2</sup>
Connection 1	B, Ind.-0°-Female, angled, 3-pin
Connection 2	M12x1-Male, straight, 3-pin, A-coded
Number of conductors	3
System	Molded/Molded

## Electrical data

Operating voltage Ub	24 VDC / 24 VAC
Rated current (40 °C)	4.0 A
Suppressor	Suppressor diode

## Environmental conditions

Cable temperature, fixed routing	-40...105 °C
Cable temperature, flexible routing	5...105 °C
IP rating	IP67/IP67, IP69K

## Material

Cable jacket, material	PVC
Material contact carrier	PBT/TPU
Material contacts	Brass/Bronze
Material cover nut	Brass
	nickel plated
Material grip	PUR/PUR
Material locking screw	Steel

## Mechanical data

Cable jacket, color	gray
Cable length L	1.00 m
Tightening torque pigtail	0.5 Nm/0.6 Nm


Double-Ended Cordsets  
**BCC VB43-M413-3E-666-VX8350-010**  
**Order Code: BCC0673**




**Remarks**

Oil resistant per DIN EN 60811-404 (VDE 0473-811-404)  
 Flame resistance per IEC 60332-1-2  
 \* style B industry standard  
 Enclosure rating per IEC 60529 or 20653, only in screwed state with the associated mating piece.

**Connector Drawings**



I  
 PIN 1: brown  
 PIN 2: blue  
 PIN PE: green/yellow



II  
 PIN 3: blue  
 PIN 4: brown  
 PIN 5: green/yellow

**Wiring Diagrams**

