

### Basic features

Approval/Conformity	CE EAC WEEE
---------------------	-------------------

### Electrical connection

Bending radius min., fixed cable	5 x D
Bending radius min., flexible cable	10 x D
Cable	PVC gray, 2.00 m
Cable diameter D	5.00 mm ±0.20 mm
Conductor cross-section	0.50 mm <sup>2</sup>
Connection	C, Ind.-0°/180°-Valve connector, right-angle, 4-pin
Connector configuration	right-angle
Number of conductors	3
Number of pins	4
System	Molded

### Electrical data

Operating voltage $U_b$	24 VDC / 24 VAC
Rated current (40 °C)	4.0 A
Suppressor	Suppressor diode

### Environmental conditions

Cable temperature, fixed routing	-40...105 °C
Cable temperature, flexible routing	-5...105 °C
IP rating	IP67

### Material

Cable jacket, material	PVC
Material contact carrier	PBT
Material contacts	Brass
Material grip	TPU
Material locking screw	Steel


### Mechanical data

Cable jacket, color	gray
Cable length L	2.00 m
Tightening torque pigtail	0.5 Nm

Remarks

Flame resistance per IEC 60332-1-2  
\* style C industry standard  
Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

Connector Drawings



PIN 1: brown  
PIN 2: blue  
PIN PE: green/yellow

Wiring Diagrams

