



## Basic features

Approval/Conformity	EAC
	cULus
	CE
	WEEE
Basic standard	IEC 60947-5-2

## Display/Operation

Function indicator	yes
Power indicator	no

## Electrical connection

Connection	M12x1-Male, 4-pin, A-coded
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

## Electrical data

Load capacitance max. at $U_e$	0.5 $\mu$ F
Min. operating current $I_m$	0 mA
No-load current $I_o$ max., damped	3 mA
No-load current $I_o$ max., undamped	9 mA
Operating voltage $U_b$	10...30 VDC
Output resistance $R_a$	33.0 kOhm + D
Protection class	II
Rated insulation voltage $U_i$	250 V AC
Rated operating current $I_e$	200 mA
Rated operating voltage $U_e$ DC	24 V
Rated short circuit current	100 A
Ready delay $t_v$ max.	20 ms
Residual current $I_r$ max.	20 $\mu$ A
Ripple max. (% of $U_e$ )	15 %
Switching frequency	1500 Hz
Utilization category	DC -13
Voltage drop static max.	2.5 V

## Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 $g_n$ , 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
IP rating	IP68

## Functional safety

MTTF (40 °C)	830 a
--------------	-------

Inductive Sensors  
**BES M08EE-POC20B-S04G**  
Order Code: BES0144

# BALLUFF

## Material

Housing material	Stainless steel
Material sensing surface	PBT

## Mechanical data

Dimension	Ø 8 x 43 mm
Installation	for flush mounting
Size	M8x1
Tightening torque	8 Nm

## Output/Interface

Switching output	PNP normally closed (NC)
------------------	--------------------------

## Range/Distance

Assured operating distance Sa	1.6 mm
Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance Sn	2 mm
Real switching distance sr	2 mm
Repeat accuracy max. (% of Sr)	5.0 %
Switching distance marking	■ ■
Temperature drift max. (% of Sr)	10 %
Tolerance Sr	±10 %

## Remarks

The sensor is functional again after the overload has been eliminated.  
For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

## Connector Drawings



## Wiring Diagrams

