



## Basic features

Approval/Conformity	CE EAC cULus WEEE
Basic standard	IEC 60947-5-2

## Display/Operation

Function indicator	yes
Power indicator	no

## Electrical connection

Cable diameter D	3.0 mm
Cable length L	0.3 m
Conductor cross-section	0.14 mm <sup>2</sup>
Connection	M8x1-Male, 3-pin
Connection type	Cable with connector, 0.30 m, PUR
Number of conductors	3
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

## Electrical data

Load capacitance max. at U <sub>e</sub>	1.0 μF
No-load current I <sub>o</sub> max., damped	2 mA
No-load current I <sub>o</sub> max., undamped	7 mA
Operating voltage U <sub>b</sub>	10...30 VDC
Output resistance R <sub>a</sub>	33.0 kOhm
Protection class	II
Rated insulation voltage U <sub>i</sub>	250 V AC
Rated operating current I <sub>e</sub>	200 mA
Rated operating voltage U <sub>e</sub> DC	24 V
Rated short circuit current	100 A
Ready delay t <sub>v</sub> max.	25 ms
Residual current I <sub>r</sub> max.	10 μA
Ripple max. (% of U <sub>e</sub> )	10 %
Switching frequency	5000 Hz
Utilization category	DC -13
Voltage drop static max.	2.5 V

## Environmental conditions

Ambient temperature	-40...85 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 g <sub>n</sub> , 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
IP rating	IP68

## Functional safety

MTTF (40 °C)	595 a
--------------	-------

Inductive Sensors  
**BES 516-377-EO-C-S49-00,3**  
Order Code: BES01LN

# BALLUFF

## Material

Housing material	Stainless steel
Jacket material	PUR
Material sensing surface	PBT

## Mechanical data

Dimension	Ø 8 x 45 mm
Installation	for flush mounting
Size	M8x1
Tightening torque	8 Nm

## Output/Interface

Switching output	PNP normally closed (NC)
------------------	--------------------------

## Range/Distance

Assured operating distance Sa	1.2 mm
Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance Sn	1.5 mm
Real switching distance sr	1.5 mm
Repeat accuracy max. (% of Sr)	5.0 %
Switching distance marking	■
Temperature drift max. (% of Sr)	10 %
Tolerance Sr	±10 %

## Remarks

The sensor is functional again after the overload has been eliminated.  
For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

## Connector Drawings



## Wiring Diagrams

