



4MT5
(CYJV CABLE ASSEMBLY)



Basic features

| | |
|---------------------|----------------------|
| Approval/Conformity | cULus EAC WEEE |
|---------------------|----------------------|

Electrical connection

| | |
|-------------------------------------|--|
| Bending radius min., fixed cable | 5 x D |
| Bending radius min., flexible cable | 10 x D |
| Cable | TPE Yellow, 20.00 m, Drag chain compatible |
| Cable diameter D | 5.30 mm ±0.13 mm |
| Cable, bending cycles min. | 10 million |
| Conductor cross-section | 22 AWG |
| Connection | M12x1-Female, Straight, 5-pin, A-coded |
| Connector configuration | Straight |
| Number of conductors | 4 |
| Number of pins | 5 |
| System | Molded |

Electrical data

| | |
|-----------------------------|-------------------|
| Cable rated voltage AC max. | 300 V |
| Cable rated voltage DC max. | 300 V |
| Operating voltage Ub | 250 VDC / 250 VAC |
| Rated current (40 °C) | 4.0 A |

Remarks

Cable construction acc. to UL-AWM Style 20327
 Flame resistance acc. to IEC 332-2
 Enclosure rating per IEC 60529 or 20653, only in screwed state with the associated mating piece.

Environmental conditions

| | |
|-------------------------------------|-------------------|
| Cable temperature, fixed routing | -50...105 °C |
| Cable temperature, flexible routing | -25...105 °C |
| Protection degree | IP67, IP68, IP69K |

Material

| | |
|--------------------------|---------------|
| Cable jacket, material | TPE |
| Material contact carrier | PUR |
| Material contacts | Bronze |
| Material cover nut | Die-cast zinc |
| Material grip | TPE |


Mechanical data

| | |
|---------------------------|-----------------------|
| Cable jacket, color | Yellow |
| Cable length L | 20.00 m |
| Cable properties | Drag chain compatible |
| Tightening torque pigtail | 0.6 Nm |

Output/Interface

| | |
|------------------|---------------|
| Switching output | Complementary |
|------------------|---------------|

Connector Drawings



PIN 1: brown

PIN 2: white

PIN 3: blue

PIN 4: black

Wiring Diagrams

