



1) Reference edge, 2) Mark. Safety switch position, 3) 1st pos., 4) Function Indicator FC



### Basic features

Approval/Conformity	CE WEEE
Basic standard	IEC 60947-5-1
Operating principle	1-6. Switch position: Mechanical
Version	Safety EN 60204-1

### Display/Operation

Function indicator	1-6. Switch position: FC - 6...24 V
--------------------	-------------------------------------

### Electrical connection

Connection type	1-6. Switch position: Screw terminal
-----------------	--------------------------------------

### Electrical data

Continuous current	1-6. Switch position: 6 A
Rated operating voltage U <sub>e</sub>	1-6. Switch position: 250 V AC
Switching function mechanical	NC forced-opening per VDE Double-interrupting Normally open with snap funct. galvanically isolated One NO and one NC Dual changeover
Switching rate	1-6. Switch position: 160/min

### Environmental conditions

Ambient temperature	-5...85 °C
IP rating	IP67

### Functional safety

B10d (EN ISO 13849-1)	BSE 85: 1 mil. Switching operations
-----------------------	-------------------------------------

### Material

Housing material	Aluminum, Anodized
Housing material, surface protection	Anodized
Material contacts	1-6. Switch position: Silver
Plunger material	1-6. Switch position: Stainless steel (1.4034)

### Mechanical data

Approach direction	Vertical to mounting surface
Approach speed	1-6. Switch position: 80 m/min
Distance cam - reference edge	1-6. Switch position: 2.50...3.00 mm
Flange, feed-through	1 threaded exit M25
Installation	Horizontal
Life expectancy mechanical	1-6. Switch position: 1 million Switching operations
Number of switching positions	6x Roller bearing
Plunger style	1-6th switch position: Roller bearing
Switch actuation force	1-6. Switch position: 30 N
Switching element	1-6. Switch position: BSE 85

### Range/Distance

Reproducibility	1-6. Switch position: ±0.02 mm
-----------------	--------------------------------

## Wiring Diagrams

