

Basic features

Approval/Conformity	CE WEEE
Scope of delivery	Part label (20x) Port cover M12 (4x) Grounding strap Lock washer Short guide M4x6 screw
Style	Two-row
Supported web browsers	Google Chrome Mozilla Firefox

Display/Operation

Actuator supply UA, indicator	Green LED
IO-Link communication indicator	Green LED
Sensor supply US indicator	Green LED
Switching function display	LED yellow

Electrical connection

Connection (COM 1)	M12x1-Female, 5-pin, D-coded
Connection (COM 2)	M12x1-Female, 5-pin, D-coded
Connection (supply voltage IN)	7/8"-Male, 5-pin
Connection (supply voltage OUT)	7/8"-Female, 5-pin
Connection slots	8x M12x1-Female, 5-pin, A-coded
Contact, surface protection	nickel plated 2 µm/gold plated 0.4 µm

Electrical data

Configurable inputs/outputs	yes
Current sum UA, actuator	9.0 A
Current sum US, sensor	9.0 A
IO-Link function	Master
Operating voltage Ub	18...30.2 VDC
Output current max.	2 A
Rated operating voltage Ue DC	24 V

Environmental conditions

Ambient temperature	-5...70 °C
EN 60068-2-6, Vibration	61...500 Hz, constant acceleration 15 g 5...61 Hz, constant amplitude 1 mm
Protection degree	IP67 when threaded in
Storage temperature	-25...70 °C

Functional safety

MTTF (40 °C)	49 a
---------------------	------

Material

Gasket, material	FKM 75
Housing material	Zinc, Die casting, Cu 15 µm, Ni 15 µm
Housing shield	yes
Surface protection	Cu 15 µm Ni 15 µm

Remarks

See short guide

For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.


Mechanical data

Dimension	68 x 37.9 x 224 mm
Mounting	2-hole screw mount
Mounting ground strap	M4

Output/Interface

Auxiliary interfaces	8x IO-Link
Digital inputs	16x PNP, Type 2
Digital outputs	16x PNP
IO-Link version	1.1
Interface	EtherCAT
Port-class	Type A

Connector Drawings



Power IN


PIN 1: 0V

PIN 2: 0V

PIN 3: Function ground

PIN 4: Sensor and bus supply.

PIN 5: Actuator supply



Power Out


PIN 1: 0V

PIN 2: 0V

PIN 3: Function ground

PIN 4: Sensor and bus supply.

PIN 5: Actuator supply




EtherCAT Port

PIN 1: TD+

PIN 2: RD+

PIN 3: TD-

PIN 4: RD-



IO-Link

PIN 1: +24V

PIN 2: In-/output/Diagnostics

PIN 3: 0V

PIN 4: IO-Link/In-/output

PIN 5: n.c.