

1) Reference edge, 2) Sealing ring, 3) Cable passage, 4) Mark. Safety switch position, 5) 1st pos.



Basic features

Approval/Conformity	CE WEEE
Basic standard	IEC 60947-5-1
Operating principle	1-3. Switch position: Mechanical with forced opening
Version	

Display/Operation

Function indicator	1-3. Switch position: None
--------------------	----------------------------

Electrical connection

Connection type	1-3. Switch position: Solder connection
-----------------	---

Electrical data

Continuous current	1-3. Switch position: 5 A
Rated operating voltage U _e	1-3. Switch position: 250 V AC
Switching function mechanical	NO forced-opening
Switching rate	1-3. Switch position: 200/min

Environmental conditions

Ambient temperature	-5...85 °C
IP rating	IP67

Functional safety

B10d (EN ISO 13849-1)	BSE 86: 10 mil. Switching operations BSE 69.1: 10 mil. Switching operations
-----------------------	--

Material



Housing material	Aluminum, Anodized
Housing material, surface protection	Anodized
Material contacts	1-3. Switch position: Silver
Plunger material	1-3. Switch position: Stainless steel (1.4034)

Mechanical data

Approach direction	longitudinal, parallel to attachment surface
Approach speed	1-3. Switch position: 20 m/min
Distance cam - reference edge	1-3. Switch position: 2.50...2.80 mm
Flange, feed-through	1 threaded exit M16
Installation	Vertical
Life expectancy mechanical	1-3. Switch position: 10 million Switching operations
Number of switching positions	3x Chisel
Plunger style	1-3rd switch position: Chisel
Switch actuation force	1-3. Switch position: 8 N
Switching element	1. Switch position: BSE 86 2-3. Switch position: BSE 69.1

Wiring Diagrams

BSE 69.1



BSE 86

