



1) Reference edge, 2) Sealing ring, 3) Cable passage, 4) Function indicator FD/FE/LL



Basic features

Approval/Conformity	CE WEEE EAC
Basic standard	IEC 60947-5-1
DIN switch	DIN 43697
Operating principle	1-12. Switch position: Mechanical
Version	Snap contact

Display/Operation

Function indicator	1-12. Switch position: FE - 90... 250 V
---------------------------	--

Electrical connection

Connection type	1-12. Switch position: Screw terminal
------------------------	--

Electrical data

Continuous current	1-12. Switch position: 6 A
Rated operating voltage Ue	1-12. Switch position: 250 V AC
Switching function mechanical	Double-interrupting galvanically isolated One NO and one NC Dual changeover
Switching rate	1-12. Switch position: 300/min

Environmental conditions

Ambient temperature	-5...85 °C
IP rating	IP67

Functional safety

B10d (EN ISO 13849-1)	BSE 30.0: 30 mil. Switching operations
------------------------------	---

Material

Housing material	Aluminum, Anodized
Housing material, surface protection	Anodized
Material contacts	1-12. Switch position: Silver, gold plated
Plunger material	1-12. Switch position: Stainless steel (1.4034)

Mechanical data

Approach direction	longitudinal, parallel to attachment surface
Approach speed	1-12. Switch position: 60 m/min
Distance cam - reference edge	1-12. Switch position: 4.50...5.00 mm
Flange, feed-through	2 threaded exit M25
Installation	Vertical
Life expectancy mechanical	1-12. Switch position: 30 million Switching operations
Number of switching positions	12x Roller
Plunger style	1-12th switch position: Roller
Switch actuation force	1-12. Switch position: 20 N
Switching element	1-12. Switch position: BSE 30.0

Range/Distance

Reproducibility	1-12. Switch position: ±0.01 mm
------------------------	---------------------------------

Wiring Diagrams

BSE 30.0

