



1) Reference edge, 2) Mark. Safety switch position



Basic features

Approval/Conformity	CE WEEE EAC
Basic standard	IEC 60947-5-1
Operating principle	1. Switch position: Mechanical with forced opening
Version	

Display/Operation

Function indicator	1. Switch position: None
---------------------------	--------------------------

Electrical connection

Connection type	1. Switch position: Solder connection
------------------------	---------------------------------------

Electrical data

Continuous current	1. Switch position: 5 A
Rated operating voltage Ue	1. Switch position: 250 V AC
Switching function mechanical	NO forced-opening
Switching rate	1. Switch position: 200/min

Environmental conditions

Ambient temperature	-5...85 °C
IP rating	IP67

Functional safety

B10d (EN ISO 13849-1)	BSE 86: 10 mil. Switching operations
------------------------------	--------------------------------------

Material

Housing material	Aluminum, Anodized
Housing material, surface protection	Anodized
Material contacts	1. Switch position: Silver
Plunger material	1. Switch position: Stainless steel (1.4034)

Mechanical data

Approach direction	longitudinal, parallel to attachment surface
Approach speed	1. Switch position: 20 m/min
Distance cam - reference edge	1. Switch position: 2.50...2.80 mm
Flange, feed-through	None
Life expectancy mechanical	1. Switch position: 10 million Switching operations
Number of switching positions	1x Chisel
Plunger style	1st switch position: Chisel
Switch actuation force	1. Switch position: 8 N
Switching element	1. Switch position: BSE 86

Range/Distance

Reproducibility	1. Switch position: ±0.02 mm
------------------------	------------------------------

Wiring Diagrams

