

1) not included in scope of delivery, 2) Distance to tape, 3) Tape, 4) LED function indicator, 5) Active measurement surface



### Basic features

<b>Additional features 01</b>	Real-time capable
<b>Application</b>	linear/rotary motion
<b>Approval/Conformity</b>	cURus CE EAC WEEE
<b>Measuring principle</b>	absolute measuring system
<b>Series</b>	S1G

### Electrical data

<b>Current consumption max. at 24 V DC</b>	70 mA
<b>Current consumption max. at 5 V DC</b>	220 mA
<b>Hysteresis H max.</b>	2 $\mu$ m
<b>Operating voltage <math>U_b</math></b>	4.75...5.25 VDC/10...28 VDC
<b>Overvoltage protection</b>	no
<b>Power consumption</b>	$\leq$ 1.5 W (no load)
<b>Switch-on delay max.</b>	1000 ms
<b>Voltage-proof up to (GND to housing)</b>	500 V DC

### Display/Operation

<b>Function indicator</b>	Green LED LED yellow LED red
---------------------------	------------------------------------

### Electrical connection

<b>Connection</b>	Connector, M12x1-Male, 12-pin
<b>Connection version</b>	axial
<b>Polarity reversal protected</b>	no

Magnetically Coded Sensors  
**BML-S1G0-Q71E-M5EZ-G0-S284**  
 Order Code: BML094Y

**BALLUFF**

**Environmental conditions**

Altitude max.	2000 m
Ambient temperature	-20...70 °C
EN 55016-2-3, Radiation	Industrial areas
EN 60068-2-27, Continuous shock	150 g, 2 ms
EN 60068-2-27, Shock	100 g, 6 ms
EN 60068-2-6, Vibration	20 g, 10...2000 Hz
EN 60068-2-64, Noise	20 g, 5...2000 Hz
EN 61000-4-2, ESD	Severity Level 4
EN 61000-4-3, RFI	Severity Level 3
EN 61000-4-4, Burst	Severity Level 3
EN 61000-4-5, Surge	Severity Level 2
EN 61000-4-6, High-frequency fields	Severity Level 3
EN 61000-4-8 Magnetic fields	Severity Level 5
Ext. magnetic fields max., in operation	1 mT (no effect)
IP rating IEC 60529 (connector)	IP67
Relative humidity	≤ 90 %, non-condensing
Storage temperature	-25...85 °C
Temperature coefficient, overall system	10.5 ppm/K

**Functional safety**

MTTF (40 °C)	88 a
--------------	------

**Material**

Housing material	Die-cast zinc, nickel plated, Chrome-plated
Housing material, surface protection	nickel plated Chrome-plated

**Mechanical data**

Diameter min.	243 mm
Dimension	16 x 18.5 x 80.3 mm
Lateral offset (Y)	±0.5 mm
Mounting	Through-hole 4.3 mm
Pitch max.	±0.5 °
Pole width	2 mm
Procedure direction	Lengthwise to tape
Roll max.	±0.5 °
Tangential offset (X) max.	±0.5 mm
Weight	78 g
Yaw max. ±	0.2 °


**Output/Interface**

Count direction	rising
Differential signals	yes
Error signal	yes
Interface	Absolute quadrature
Preset	configurable via hardware PIN or software tool
Real-time signals	Digital A/B, RS422
Signal sequence	A before B = rising

**Range/Distance**

Edge separation min.	0.94 µs
Interpolation factor	1000
Measuring range	48 m
Non-linearity of sensor head, max.	±2 µm
Optimal read distance	0.4 mm
Read distance	0.01...0.8 mm
Repeat accuracy	≤ 1 µm
Resolution	2 µm
Traverse speed max., absolute interface	1.2 m/s

**Connector Drawings**



## Wiring Diagrams

Pin	Signal
1	+B
2	-B
3	+VH Req
4	-VH Req
5	-Z/-VH Busy
6	+Z/+VH Busy

Pin	Signal
7	GND
8	V DC
9	-A
10	+A
11	PRESET
12	NC
Shield	Shield