

1) not included in scope of delivery, 2) Distance to tape, 3) Tape, 4) LED function indicator, 5) Active measurement surface



### Basic features

<b>Additional features 01</b>	Real-time capable
<b>Additional features 02</b>	Analog, sin/cos
<b>Application</b>	linear/rotary motion
<b>Approval/Conformity</b>	cURus CE EAC WEEE
<b>Measuring principle</b>	absolute measuring system
<b>Series</b>	SL1

### Electrical data

<b>Hysteresis H max.</b>	1 µm
<b>Operating voltage U<sub>b</sub></b>	18...30 VDC
<b>Output value</b>	Position in µm
<b>Overvoltage protection</b>	no
<b>Periods</b>	2 mm
<b>Power consumption</b>	≤ 1.4 W (no load)
<b>Switch-on delay max.</b>	100 ms
<b>Voltage-proof up to (GND to housing)</b>	500 V DC

### Display/Operation

<b>Error value</b>	0x7FFFFFFC
<b>Function indicator</b>	Green LED LED yellow LED red

### Electrical connection

<b>Connection</b>	Connector, M12x1-Male, 12-pin
<b>Connection version</b>	axial
<b>Polarity reversal protected</b>	yes

Magnetically Coded Sensors  
**BML SL1-ALZ1-UEZZ-AU1L-S284**  
 Order Code: BML0902



**Environmental conditions**

Altitude max.	2000 m
Ambient temperature	-20...70 °C
EN 55016-2-3, Radiation	Industrial areas
EN 60068-2-27, Continuous shock	150 g, 2 ms
EN 60068-2-27, Shock	100 g, 6 ms
EN 60068-2-6, Vibration	20 g, 10...2000 Hz
EN 60068-2-64, Noise	20 g, 5...2000 Hz
EN 61000-4-2, ESD	Severity Level 4
EN 61000-4-3, RFI	Severity Level 3
EN 61000-4-4, Burst	Severity Level 3
EN 61000-4-5, Surge	Severity Level 2
EN 61000-4-6, High-frequency fields	Severity Level 3
EN 61000-4-8 Magnetic fields	Severity Level 5
Ext. magnetic fields max., in operation	1 mT (no effect)
IP rating IEC 60529 (connector)	IP67
Relative humidity	≤ 90 %, non-condensing
Storage temperature	-25...85 °C
Temperature coefficient, overall system	10.5 ppm/K

**Functional safety**

MTTF (40 °C)	149 a
--------------	-------

**Material**

Housing material	Die-cast zinc, nickel plated, Chrome-plated
Housing material, surface protection	nickel plated Chrome-plated

**Mechanical data**

Diameter min.	400 mm
Dimension	16 x 18.6 x 54 mm
Lateral offset (Y)	±1.5 mm
Mounting	Through-hole 4.3 mm
Pitch max.	±0.5 °
Pole width	2 mm
Procedure direction	Lengthwise to tape
Roll max.	±0.5 °
Tangential offset (X) max.	±1 mm
Weight	50 g
Yaw max. ±	1.0 °


**Output/Interface**

Count direction	rising
Cycle time min.	1 ms
Data format	32-bit signed
Differential signals	yes
Error signal	yes
Interface	IO-Link 1.1
Interface coding	Binary
Real-time signals	Analog, sin/cos
Signal sequence	A before B = rising

**Range/Distance**

Interpolation factor	2000
Measuring range	8190 mm
Non-linearity of sensor head, max.	±5 µm
Optimal read distance	0.4 mm
Read distance	0.01...1.3 mm
Repeat accuracy	≤ 1 µm
Resolution	1 µm
Traverse speed max.	10 m/s

**Connector Drawings**



## Wiring Diagrams

Pin	
1	+B(+Cos)
2	-B(-Cos)
3	NC
4	NC
5	C/Q
6	NC

Pin	
7	L- (0 V)
8	L+ (18...30 V)
9	-A(-Sin)
10	+A(+Sin)
11	NC
12	NC